## INDIUM CORPORATION®

## **PRODUCT DATA SHEET**

# Ball-Attach Flux WS-575-C

#### **Features:**

- Halogen-free no intentionally added (NIA) halogens
- Flux rheology applicable for all sphere sizes
- · Suitable for Pb-free applications
- · Uniform pin transfer over extended periods
- Low voiding
- No "missing ball"
- Excellent solderability on a wide range of surfaces
- · Cleanable with DI water only

#### Introduction

**Ball-Attach Flux WS-575-C** is a NIA halogen-free water-soluble ball-attach flux designed for use in pin-transfer applications for ball attachment to substrates (BGA manufacturing). Its rheology is specifically designed for use with even the smallest gravity-fed spheres. **WS-575-C** has an activator system powerful enough to promote wetting on the most demanding substrate metallizations. **WS-575-C** is cleanable with just DI water only.

#### **Properties**


Property	Value	Test Method
Flux Type Classification:	ORHO	J-STD-004 (IPC-TM-650:2.3.32 and 2.3.33)
Typical Viscosity:	14kcps (peak) 13kcps (5mins)	Brookfield HB DVII +-CP (5rpm)
SIR (ohms, after cleaning):	Pass (>10 <sup>8</sup> after 7 days @85°C & 85% RH)	J-STD-004 (IPC-TM-650: 2.6.33 IPC-B-24)
Typical Acid Number:	95mg KOH/g	Titration
Typical Tack Strength:	330g	J-STD-005 (IPC-TM-650:2.4.44)
Shelf Life:	<-5°C for 3 months	Viscosity change / microscope examination

All information is for reference only. Not to be used as incoming product specifications.



## **Application**

The amount of **WS-575-C** flux deposited on the substrate can be optimized by changing equipment parameters. Key variables include pin shape, pin diameter, shear speed, dwell, and depth of immersion. The flux rheology can be optimized for desired application by shearing to achieve the desired viscosity.



#### Cleaning

**WS-575-C** residue can be cleaned with DI water or water with an added cleaner. Ideal conditions for spray-cleaning: 20–30°C for >1 minute at >60psi.

OVER→

Form No. 99110 (A4) R2

www.indium.com askus@indium.com

ASIA: Singapore, Cheongju, Malaysia: +65 6268 8678 CHINA: Suzhou, Shenzhen: +86 (0)512 628 34900 EUROPE: Milton Keynes, Torino: +44 (0) 1908 580400 USA: Utica, Clinton, Chicago, Rome: +1 315 853 4900





## INDIUM CORPORATION®

## **Ball-Attach Flux WS-575-C**

## **Packaging**

**Ball Attach Flux WS-575-C** is available in jars and in 6 oz. and 12 oz. cartridges.

#### **Storage**

For maximum shelf life, **WS-575-C** cartridges should be stored tip down at < -5 °C. Storage temperatures should not exceed 25 °C for more than 4 days, and should never exceed 30 °C. After removing from cold storage, **WS-575-C** should be allowed to stand for at least 4 hours at room temperature before using.


#### **Technical Support**

Indium Corporation sets the industry standard in providing rapid response, on-site technical support for our customers worldwide. Indium Corporation's team of Technical Support Engineers can provide expertise in all aspects of materials science and semiconductor packaging process applications.

#### **Safety Data Sheets**

The SDS for this product can be found online at http://www.indium.com/sds

#### Reflow



A short preheat  $(150\,^{\circ}\text{-}160\,^{\circ}\text{C})$  for less than 45 seconds may be used to reduce voiding. The profile should ideally be a linear ramp at 1-2  $^{\circ}\text{C}/\text{second}$  up to 20-30  $^{\circ}\text{C}$  above solidus temperature, with a rapid cool down afterwards, and a minimum time above liquidus of 20 seconds.

This product data sheet is provided for general information only. It is not intended, and shall not be construed, to warrant or guarantee the performance of the products described which are sold subject exclusively to written warranties and limitations thereon included in product packaging and invoices. All Indium Corporation's products and solutions are designed to be commercially available unless specifically stated otherwise.

#### www.indium.com askus@indium.com

ASIA: Singapore, Cheongju, Malaysia: +65 6268 8678 CHINA: Suzhou, Shenzhen: +86 (0)512 628 34900 EUROPE: Milton Keynes, Torino: +44 (0) 1908 580400 USA: Utica, Clinton, Chicago, Rome: +1 315 853 4900



